
# CARLO Alu, Classic 185

# beka different By design

IL









## A safe and reliable passive lift for your residents.

Our mobile sling lift CARLO Alu, Classic 185, provides your care staff with optimum support for all daily lifting and transfer routines and enables them to work ergonomically, safely and efficiently at all times without placing additional strain on the musculoskeletal system by manually lifting and repositioning the resident.

The extending arm with 4-point loop bar can be lowered to the floor using the hand control, ensuring that a person who has fallen from the floor can be picked up safely and easily by just one carer. The chassis can be spread electrically and therefore offers a high level of operating comfort. Due to the low height of the chassis, the CARLO Alu, Classic 185 model, can easily be used to drive under both bathtubs and care beds.

#### Watch product video!





#### **Technichal Data**

	Chassis (W x H )	1
	Width inside ( closed/spread )	5
	Width outside ( closed/spread )	7
	Stroke	1
	SWL	1

#### Product information

Stable aluminum-st
Hand control with battery
4-point loop handle with sa
Electric height adjustment and e
Anti-rotation med

#### Available Options



Digital patient scale

**Clip Slings** 



Transfer slings With headrest Padded leg loops High quality nylon material



Toilet slings With headrest Padded leg loops Arm padding

### Stable 4-point loop bar

The CARLO Alu, Classic 185 belt bar is suitable for all loop belts and has a safety locking mechanism for the belt holder. The distance between the mounting bar and the lifting pole is large so that residents have more space during the transfer.

#### Anti-rotation mechanism

The anti-rotation mechanism (ARM) prevents unpleasant swinging or rotating movements during lifting and transfer.



#### Ideal for bathing and showering

The passive lift can be used in the bathroom without restriction by using high-quality aluminum, both for showering and bathing your residents. The extremely lightweight design makes it easy to maneuver without any effort. You can purchase the appropriate (bath) straps from us.



- > Quick & easy replacement of the bar
- > Table with 8-point suspension
- > Table with and without level compensation



1.400 mm x 125 mm		
540 mm / 1.040 mm		
700 mm / 1.180 mm		
1.400 mm		
185 kg		

eel construction

charge status display

fety locking mechanism

lectrically spreadable chassis

hanism (ARM)



Wall charging unit





Bathing slings

Vith headrest Padded leg loops High quality nylon-mesh material



Soft slings With headrest Padded leg loops Breathable nylon/cotton blend



BEKA Hospitec GmbH | Am Rübenmorgen 3 | 35582 Wetzlar-Dutenhofen Tel +49 641 922 20-0 | E-Mail info@beka-hospitec.com www.beka-hospitec.com